

## PRODUCT DATA SHEET

Standing: 2024-01-18

LAUDA Puridest PD 2 R  
Water still 230 V; 50/60 Hz  
Part Number: L003220

### Features

- Water Still for single distillation (fully automatic) with storage tank, suitable for both bench and wall mounting
- The distillate storage tank accepts twice the hourly capacity of the still
- Distillate withdrawal through drain cock with continuous and touch position.
- Condenser (cooling coil) inside the storage tank, easily exchangeable.
- Solenoid valve to control the water supply
- Economical energy consumption by distillation of the heated cooling water.
- Water saving through automatic water cut-off. Unnecessary water consumption will be avoided.
- Evaporator easily accessible for cleaning purposes.
- CO<sub>2</sub> degassing through outlet in the condenser.
- Electronic contamination monitoring of the still with distillation stop and visual cleaning instruction
- Automatic refill of the storage tank after distillate removal, controlled by electronic level detection
- Thermostatic low water cut-off
- Heating element, evaporator, storage tank and condenser made of stainless steel.
- Housing made of galvanised sheet steel, powder coated
- Double-walled housing



Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Ralf Hermann, Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

# PRODUCT DATA SHEET

Standing: 2024-01-18

LAUDA Puridest PD 2 R  
 Water still 230 V; 50/60 Hz  
 Part Number: L003220

## Technical Features

Conductivity stage 1 /25 °C	2.3 µS/cm
Production output	2 L/h
Tank volume	4 L
Heater power max.	1.5 kW
Power consumption max.	1.5 kW
Cooling water flow rate	0.5 L/min
Pressure difference cooling water min.	3 bar
Maximal pressure cooling water	7 bar
Wasserkühlung Zulauf für Schlauch	1/2 "
Wasserkühlung Ablauf für Schlauch	3/4 "
Overall dimensions (WxDxH)	540 x 290 x 420 mm
Weight	15 kg
Ambient temperature range	10 ... 40 °C
Power supply	230 V; 50/60 Hz
Power plug	Power cord with angled plug (BS1363)

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
 Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
 info@lauda.de • www.lauda.de  
 WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
 Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
 LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
 Sitz Lauda-Königshofen  
 Registergericht Mannheim • HRB 560226

Geschäftsführer:  
 Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
 Dr. Ralf Hermann, Dr. Marc Stricker  
 Beirat: Dr. Gerhard Wobser