

PRODUCT DATA SHEET

Standing: 2024-04-29

LAUDA Varioshake VS 15 O
 Shaker 100 V; 50/60 Hz
 Part Number: L003206

Features

- Shaker with orbital motion, heavy duty, low noise, in a compact design
- Shaking frequency display and setting digitally via LC display, in steps of 1.0 rpm, gentle start-up
- The setpoint and actual values as well as the shaking frequency are displayed on two LC displays
- User-friendly microprocessor technology
- Membrane keyboard with distinctive symbols.
- Timer adjustable from 1 min. up to 99:59 hours or continuous operation
- Optional RS 232 interface on request
- Shaking table made of anodized aluminum with four plastic pins
- Drive by an overload-protected AC motor
- Compact, low-wear mechanism with mass balancing for a secure stand
- Constant speed, independent of load
- Excellent for continuous use
- Outer housing made of electrolytically galvanized sheet steel, powder-coated



Technical Features

Ambient temperature range	10 ... 50 °C
Shaking tray (WxD)	450 x 450 mm
Power consumption max.	0.07 kW
Shaking amplitude	30 mm
Shaking frequency	20 ... 300 1/min
Load max.	15 kg
Overall dimensions (WxDxH)	480 x 487 x 160 mm
Weight	18 kg
Power plug	Power cord with plug (NEMA 5-15P)
Power supply	100 V; 50/60 Hz

LAUDA DR. R. WOBSEY GMBH & CO. KG
 Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
 info@lauda.de • www.lauda.de
 WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
 Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
 LAUDA DR. R. WOBSEY Verwaltungs-GmbH
 Sitz Lauda-Königshofen
 Registergericht Mannheim • HRB 560226

Geschäftsführer:
 Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
 Dr. Ralf Hermann, Dr. Marc Stricker
 Beirat: Dr. Gerhard Wobser