

PRODUCT DATA SHEET

Standing: 2025-02-12

LAUDA Varioshake VS 8 B

Shaker 230 V; 50/60 Hz

Part Number: L003138

Features

- Shaker with bidirectional motion, heavy-duty, low-noise in a compact design
- Shaking frequency display and setting digitally via LC display, in steps of 1.0 rpm, gentle start-up
- The setpoint and actual values as well as the shaking frequency are displayed on two LC displays
- User-friendly microprocessor technology
- Membrane keyboard with distinctive symbols.
- Timer adjustable from 1 min. up to 99:59 hours or continuous operation
- Optional RS 232 interface on request
- Shaking table made of anodized aluminum with four plastic pins
- Drive by an overload-protected AC motor
- Compact, low-wear mechanism with mass balancing for a secure stand
- Constant speed, independent of load
- Excellent for continuous use
- Outer housing made of electrolytically galvanized sheet steel, powder-coated



Technical Features

| | |
|----------------------------|--|
| Ambient temperature range | 10 ... 50 °C |
| Shaking platform (WxD) | 330 x 330 mm |
| Power consumption max. | 0.07 kW |
| Shaking amplitude | 20 mm |
| Shaking frequency | 20 ... 300 1/min |
| Load max. | 8 kg |
| Overall dimensions (WxDxH) | 350 x 355 x 160 mm |
| Weight | 11 kg |
| Power plug | Power cord with plug (SEV 1011, SEV 5934/2, T23) |
| Power supply | 230 V; 50 Hz |

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunter Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser