

PRODUCT DATA SHEET

Standing: 2024-10-14

LAUDA Varioshake VS 8 B

Shaker 230 V; 50/60 Hz

Part Number: L003164

Features

- Shaker with bidirectional motion, heavy-duty, low-noise in a compact design
- Shaking frequency display and setting digitally via LC display, in steps of 1.0 rpm, gentle start-up
- The setpoint and actual values as well as the shaking frequency are displayed on two LC displays
- User-friendly microprocessor technology
- Membrane keyboard with distinctive symbols.
- Timer adjustable from 1 min. up to 99:59 hours or continuous operation
- Optional RS 232 interface on request
- Shaking table made of anodized aluminum with four plastic pins
- Drive by an overload-protected AC motor
- Compact, low-wear mechanism with mass balancing for a secure stand
- Constant speed, independent of load
- Excellent for continuous use
- Outer housing made of electrolytically galvanized sheet steel, powder-coated



Technical Features

Ambient temperature range	10 ... 50 °C
Shaking platform (WxD)	330 x 330 mm
Power consumption max.	0.07 kW
Shaking amplitude	20 mm
Shaking frequency	20 ... 300 1/min
Load max.	8 kg
Overall dimensions (WxDxH)	350 x 355 x 160 mm
Weight	11 kg
Power plug	Power cord with plug (AS/NSZ 3112)
Power supply	230 V; 50/60 Hz

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser